



Actual

Catalog Number: TC5140-NDT
Product ID: 7TAG009660R0016
UPC Number: 78620901919
EAN Number: 05415022361025
Status: A

Detectable Saddle Support Mounting Base, Detectable Blue Nylon, Length of 14.22mm (0.56 Inches), Width of 8.64mm (0.34 Inches), Screw Mounting Method, #4 Pan Head Screw, 100 Pack

- Detectable with metal and X-ray detection equipment.
- This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Saddle Support Base
Special Features	Detectable with metal and X-ray detection equipment.
Material	Nylon/Polyamide 6.6
Color	Blue
Mounting	Screw
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	14.22mm
Width	8.64mm
Type of fastening	Other
Material	Plastic
Material quality	Polyamide PA
Colour	Blue

Packaging

Inner Quantity	100
Inner Dimensions (inches)	8x4x1
Outer Quantity	500
Outer Dimensions (inches)	9.25x8x5
Weight Uom	1.25 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001086
--------------------------------	------------