



Representative

**Catalog Number:** TC5142X  
**Product ID:** 7TAG009840R0018  
**UPC Number:** 78620987439  
**EAN Number:** 05414363491224  
**Status:** A

Saddle Support Mounting Base, Heat Stabilized Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length of 23.42mm (0.922 Inches), Width of 14.29mm (0.563 Inches), Height of 10.72mm (0.422 Inches), Mount with #10 Screw, 100 Pack

- This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.

#### North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Saddle Support Base
Special Features	This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.
Material	Nylon/Polyamide 6.6
Color	Black
Mounting	Screw
Operating Temperature	-40 to +185 F

#### European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	23.42mm
Width	14.29mm
Height	10.72mm
Suitable for cable tie width to	7.6mm
Type of fastening	Other
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+105°C
Colour	Black

#### Packaging

Inner Quantity	100
Inner Dimensions (inches)	4.5x7x2
Outer Quantity	500
Outer Dimensions (inches)	9.5x9.5x4.75
Weight Uom	1.88 lbs. per 1000

#### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------