



Actual

Catalog Number: TC5342A
Product ID: 7TAG009800R0000
UPC Number: 78621080692
EAN Number: 05414363058892
Status: A

Two-Way Mounting Base, Natural Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Height of 6.4mm (0.25 Inches), Self-Adhesive Mounting Method, 100 Pack

- One-piece molding - no lost parts

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	One-piece molding - no lost parts
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Self-Adhesive
Operating Temperature	-32 to +150 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	28.58mm
Width	28.58mm
Height	6.35mm
Suitable for cable tie width to	4.8mm
Type of fastening	Self-adhesive
Material	Plastic
Material quality	Polyamide PA
Operating temperature	0-+65°C
Colour	Natural colour

Packaging

Inner Quantity	100
Inner Dimensions (inches)	12x6x0
Outer Quantity	500
Outer Dimensions (inches)	9.75x7.75x6.75
Weight Uom	0.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------