



Actual

Catalog Number: TC5345AX
Product ID: 7TAG009800R0005
UPC Number: 78621076284
EAN Number: 05414363058960
Status: A

Four-Way Adhesive Mounting Base, Black Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Weather and UV Resistant, Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Height of 5.7mm (0.22 Inches), Self-Adhesive Mounting Method

- Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.
Number Of Entries	4
Material	Nylon/Polyamide 6.6 Weather Resistant
Color	Black
Mounting	Self-Adhesive
Operating Temperature	-32 to +150 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	28.58mm
Width	28.58mm
Height	5.08mm
Suitable for cable tie width to	5.2mm
Type of fastening	Other
Material	Plastic
Material quality	Polyamide PA
Operating temperature	0-+65°C
Colour	Black

Packaging

Inner Quantity	100
Inner Dimensions (inches)	10.5x8x.16
Outer Quantity	500
Outer Dimensions (inches)	9.2x9x4.7
Weight Uom	7.5 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000068
--------------------------------	------------