



Actual

Catalog Number: TC503
Product ID: 7TAG009870R0001
UPC Number: 78621080483
EAN Number: 05414363058816
Status: A

Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 79mm (3.11 Inches), Width of 15.8mm (0.622 Inches), Height of 5.1mm (0.201 Inches), Screw Mounting Method, 100 Pack

- These nylon bases provide a mounting range for bundles from 1/4 to 4 inches in diameter. One mounting hole is slotted to permit adjustment of the bundle position up to the time of actual bundle installation.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	These nylon bases provide a mounting range for bundles from 1/4 to 4 inches in diameter. One mounting hole is slotted to permit adjustment of the bundle position up to the time of actual bundle installation.
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	79mm
Width	15.8mm
Height	5.1mm
Type of fastening	Other
Material	Plastic
Material quality	Polyamide PA
Colour	Natural colour

Packaging

Inner Quantity	100
Inner Dimensions (inches)	11x5.05x2.05
Outer Quantity	500
Outer Dimensions (inches)	16.3x8.3x7.8
Weight Uom	1.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------