



Actual

Catalog Number: TC5356
Product ID: 7TAG009870R0005
UPC Number: 78621080640
EAN Number: 05414363059073
Status: A

Heavy-Duty Mounting Cradle, Black Nylon 6.6 for Temperatures up to 85 Degrees Celsius, Weather and Ultraviolet Resistant, Length of 44.45mm (1.75 Inches), Width of 19.1mm (0.75 Inches), Height of 15.9mm (0.626 Inches), for Use with Lashing Ties, Screw Mounting Method, #10 Screw

- Weather-resistant nylon mounting base for use with lashing ties Cat. No. Ty-5409 (.500 wide).

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Heavy Duty Mounting Cradle
Special Features	Weather-resistant nylon mounting base for use with lashing ties Cat. No. Ty-5409 (.500 wide).
Mount Size	#10
Material	Nylon/Polyamide 6.6 Weather Resistant
Color	Black
Mounting	Screw
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	44.45mm
Width	19.1mm
Height	15.9mm
Suitable for cable tie width to	12.7mm
Type of fastening	Other
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Black

Packaging

Inner Quantity	25
Outer Quantity	250
Outer Dimensions (inches)	9.4x9.3x5.1
Weight Uom	1 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------