



Actual

**Catalog Number:** TC5358  
**Product ID:** 7TAG009850R0001  
**UPC Number:** 78621080739  
**EAN Number:** 05414363059097  
**Status:** A

Heavy-Duty Wall Plug, Black Nylon 6.6 for Temperatures up to 85 Degrees Celsius, Weather and Ultraviolet Resistant, Length of 9.9mm (0.39 Inches), Width of 9.9mm (0.39 Inches), Height of 31.8mm (1.25 Inches), to be Used with Masonry and Brick Surfaces, Hole Size in Masonry of 6.35mm (0.25 Inches)

- Range-taking base to accommodate virtually all of cable-to-masonry clamping needs. Installs simply by tapping into a drilled hole.

#### North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Heavy Duty Application
Special Features	Range-taking base to accommodate virtually all of cable-to-masonry clamping needs. Installs simply by tapping into a drilled hole.
Material	Nylon/Polyamide 6.6 Weather Resistant
Color	Black
Mounting	Push Mount
Operating Temperature	-40 to +185 F

#### European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	9.9mm
Width	9.9mm
Height	31.8mm
Suitable for cable tie width to	4.8mm
Type of fastening	Other
Diameter mounting hole	6.35mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Black

#### Packaging

Inner Quantity	100
Outer Quantity	500
Outer Dimensions (inches)	11.05x9.2x5
Weight Uom	2.5 lbs. per 1000

#### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------