



Actual

Catalog Number: TC5363X
Product ID: 7TAG009890R0003
UPC Number: 78621071568
EAN Number: 05414363059110
Status: A

Framing Channel Clamp, Black Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant, to be Used with Channel Size 38.1mm (1.5 Inches) x 41.28mm (1.625 Inches)

- Designed to protect cable insulation and hoses when fastening wire bundles to framing channel sizes 1.5 and 1.625. Indoor or outdoor use.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Heavy Duty Application
Special Features	Designed to protect cable insulation and hoses when fastening wire bundles to framing channel sizes 1.5 and 1.625. Indoor or outdoor use.
Material	Nylon/Polyamide 6.6 Weather Resistant
Color	Black
Mounting	Push Mount
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Type of fastening	Other
Material	Plastic
Material quality	Polyamide PA
Colour	Black

Packaging

Inner Quantity	50
Outer Quantity	250
Outer Dimensions (inches)	9.2x9.2x5.2
Weight Uom	1 lbs. per 100

Documents / Support Tools

Catalog Page	Available on Website
--------------	----------------------