



Actual

Catalog Number: TC5823
Product ID: 7TAG009850R0003
UPC Number: 78621083066
EAN Number: 05414363059127
Status: A

Push-In Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 11.33mm (0.446 Inches), Width of 11.33mm (0.446 Inches), Height of 17.0mm (0.669 Inches), 100 Pack

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Push Mount
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	11.33mm
Width	11.33mm
Height	17mm
Suitable for cable tie width to	4.8mm
Type of fastening	Push fit plug
Diameter mounting hole	6.5mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

Packaging

Inner Quantity	100
Outer Quantity	500
Outer Dimensions (inches)	7.9x4.3x5.9
Weight Uom	1.25 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------