



Actual

**Catalog Number:** TC812-TB  
**Product ID:** 7TAG009880R0009  
**UPC Number:** 78621082626  
**EAN Number:** 05414363059202  
**Status:** A

Miniature Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 19.3mm (0.76 Inches), Width of 9.78mm (0.385 Inches), Height of 5.0mm (0.197 Inches), Screw Mounting Method, #10 Pan Head Screw

- These miniature mounting bases are ideal for high-density packaging. Threaded insert permits screw to come from outside of mounting surface.

**North American Specifications (UNSPSC)**

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	These miniature mounting bases are ideal for high-density packaging. Threaded insert permits screw to come from outside of mounting surface.
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

**European Specifications (ETIM)**

ETIM	EC000449 Mounting base and -element for cable ties
Length	19.3mm
Width	9.78mm
Height	5mm
Suitable for cable tie width to	4.8mm
Type of fastening	Other
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

**Packaging**

Inner Quantity	1000
Inner Dimensions (inches)	12.4x10.8x10.7
Outer Quantity	10000
Outer Dimensions (inches)	16.4x8.3x7.7
Weight Uom	0.63 lbs. per 1000

**Documents / Support Tools**

Technical Drawing / Data Sheet US Available on Website