



Actual

Catalog Number: TC815-TB
Product ID: 7TAG009880R0012
UPC Number: 78621082629
EAN Number: 05414363059233
Status: A

In-Line Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 32.0mm (1.26 Inches), Width of 19.56mm (0.77 Inches), Height of 6.6mm (0.26 Inches), Screw Mounting Method, #10 Screw

- A standard two-hole base that installs in-line with the wire bundle which conceals it.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	A standard two-hole base that installs in-line with the wire bundle which conceals it.
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	32mm
Width	19.56mm
Height	6.6mm
Suitable for cable tie width to	7.6mm
Type of fastening	Other
Diameter mounting hole	4.3mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

Packaging

Inner Quantity	500
Outer Quantity	5000
Outer Dimensions (inches)	20.8x13.1x9.1
Weight Uom	6.25 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------