



Representative

**Catalog Number:** TC823X  
**Product ID:** 7TAG009860R0008  
**UPC Number:** 78621083974  
**EAN Number:** 05414363059288  
**Status:** Active

Push-In Mounting Base, Black Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant, Length of 11.33mm (0.446 Inches), Width of 11.33mm (0.446 Inches), Height of 17.0mm (0.669 Inches)

### North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Brand Name	Ty-Rap
Type	Push-In Mounting Base
Cable Size	up to 0.189 Inch/4.8mm
Material	Nylon/Polyamide 6.6
Color	Black
Screw Holes	0.24 Inch/6.2mm to 0.256 Inch/6.5mm
Mounting	Push
Operating Temperature	-40 Degrees F/-40 C to 185 Degrees F/85 C

### European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	11.33mm
Width	11.33mm
Height	17mm
Suitable for cable tie width to	4.8mm
Type of fastening	Push fit plug
Diameter mounting hole	6.5mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Black

### Packaging

Inner Quantity	1000
Outer Quantity	10000
Outer Dimensions (inches)	12.8x10.5x10.3
Weight Uom	1.25 lbs. per 1000