



Actual

**Catalog Number:** TC826-TB  
**Product ID:** 7TAG009880R0014  
**UPC Number:** 78621082636  
**EAN Number:** 05414363075066  
**Status:** A

Cross-Fastening Screw-Mounted Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 24.31mm (0.957 Inches), Width of 13.21mm (0.52 Inches), Height of 5.97mm (0.235 Inches), Screw Mounting Method, #8 Screw, Mounting Hole Diameter of 4.4mm (0.173 Inches)

- These mounting bases can be used to tie bundles running parallel or perpendicular to length of base.

### North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	These mounting bases can be used to tie bundles running parallel or perpendicular to length of base.
Mount Size	#8
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

### European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	24.31mm
Width	13.21mm
Height	5.97mm
Suitable for cable tie width to	4.8mm
Type of fastening	Other
Diameter mounting hole	4.4mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

### Packaging

Inner Quantity	1000
Inner Dimensions (inches)	12x8.25x2.9
Outer Quantity	10000
Outer Dimensions (inches)	18.3x13.3x13.5
Weight Uom	2.12 lbs. per 1000

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website