



Actual

Catalog Number: TC5347A
Product ID: 7TAG009800R0007
UPC Number: 78621088954
EAN Number: 05414363058977
Status: A

Four-Way and Two-Way Mounting Base With Open Leg Design, Natural Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Height of 8.7mm (0.34 Inches), Self-Adhesive Mounting Method, 100 Pack

- Accommodates 4-way for ties up to .091 and 2-way for ties up to .301 maximum width.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	Accommodates 4-way for ties up to .091 and 2-way for ties up to .301 maximum width.
Number Of Entries	4
Mount Size	#8
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Self-Adhesive
Operating Temperature	-32 to +150 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	28.6mm
Width	28.6mm
Height	8.7mm
Type of fastening	Self-adhesive
Material	Plastic
Material quality	Polyamide PA
Colour	Natural colour

Packaging

Inner Quantity	100
Inner Dimensions (inches)	12x6x0
Outer Quantity	500
Outer Dimensions (inches)	10x6.7x8
Weight Uom	5 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------