



Actual

Catalog Number: TC92
Product ID: 7TAG009910R0088
UPC Number: 78621082238
EAN Number: 05414363059370
Status: A

Saddle-Type Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 15.11mm (0.595 Inches), Width of 15.11mm (0.595 Inches), Height of 14.27mm (0.562 Inches), Screw Mounting Method, #6 Screw

- Saddle Mounting Plate for use with round bundles.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	Saddle Mounting Plate for use with round bundles.
Mount Size	#6
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	15.11 mm
Width	15.11 mm
Height	14.27 mm
Type of fastening	Other
Material	Plastic
Material quality	Polyamide PA
Colour	Natural colour

Packaging

Inner Quantity	100
Inner Dimensions (inches)	7.35x5.1x2.15
Outer Quantity	1000
Outer Dimensions (inches)	16.3x8.4x7.7
Weight Uom	3.83 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website