



Catalog Number: EXS04ASC3
Product ID: 7TCA297180R0326
UPC Number: 78621019690
EAN Number: 05011949234017
Status: A

Single Compression Cable Gland, 1/2 Inch NPT Thread, For Use with All Cable Types, Flameproof Ex d and Increased Safety Ex e, Deluge Proof, IP66-68 Rating, Cable Range 6 to 12mm, Stainless Steel

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Single Compression Cable Gland
Application	For Use with All Cable to Provide Secure Cable Connections Through Knockouts and Threaded Entries
Standard	Approved to EN60079-0, 60079-1, 60079-7, 60079-31
Size	1/2 Inch NPT
Conductor Range	6 to 12 Millimeters
Material	Stainless Steel
Color	Metallic
Insulation	IP66-68 Rating
Temperature Rating	-40 to 100 C
Environmental Conditions	Flameproof Ex d

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Thread length	21mm
Hexagon angular dimension	31.5mm
Suitable for cable diameter	6.0-12.0mm
Material	Metal
Material quality	Stainless steel V4A
Surface protection	Untreated
Halogen free	N
Glass-fibre reinforced	N
Degree of protection (IP)	IP68
Shock resistant	N
Colour	Natural colour
Bend radius protection/trumpet flare	N
With locknut	N
Model	Straight
Flat cable coupling	N
Strain relief	N
Operating temperature	-40-+100°C
Explosion-tested version	Y
For Ex-zone gas	None
For Ex-Zone dust	None
EMC-version	N

Packaging

Inner Quantity	30
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	180
Outer Dimensions (inches)	3.94x15.75x11.02



Weight Uom

0.1 lbs. Each