



Representative

Catalog Number: NCG-0502G
Product ID: 7TCA303070R0193
UPC Number: 78621015337
EAN Number: 05415022425109
Status: A

Non Armoured Cable Gland, Thread Size 1/2 Inch NPT, Cable Range 6 to 12 Millimeters, Thread Length 15 Millimeters, Nylon, Grey

- Low profile compact cable glands
- Wide cable clamping range
- Good corrosion resistance

North American Specifications (UNSPSC)

| | |
|--------------------|---|
| UNSPSC | 39121431 Cable gland connector |
| IGCC | 4601 Cable gland connector |
| Type | Non Armoured Cable Gland |
| Application | General purpose, Panel building, Light fixture and housings |
| Standard | UL514B, CSA, RoHS, WEEE, LVD |
| Size | 1/2 Inch NPT |
| Conductor Range | 6 to 12 Millimeters |
| Material | Nylon |
| Color | Gray |
| NEMA Rating | 4 |
| Temperature Rating | -20 to +100 C |

European Specifications (ETIM)

| | |
|--|----------------------------|
| ETIM | EC000441 Cable screw gland |
| Thread type | NPT |
| Nominal thread size inch/gas pipe thread | 1/2 inch |
| Thread length | 15mm |
| Suitable for cable diameter | 6 - 12mm |
| Material | Plastic |
| Material quality | Polyamide (PA) |
| Halogen free | Y |
| Degree of protection (IP) | IP68 |
| Colour | Dark grey |
| Model | Straight |
| Operating temperature | -20-+100°C |

Packaging

| | |
|---------------------------|------------------|
| Inner Quantity | 10 |
| Inner Dimensions (inches) | 7.09x3.54x3.54 |
| Outer Quantity | 50 |
| Outer Dimensions (inches) | 3.94x15.75x11.02 |
| Weight Uom | 0.01 lbs. Each |

Documents / Support Tools

| | |
|--------------------------------|----------------------|
| Technical Drawing / Data Sheet | TDS000030 |
| Instruction Sheet | TA05283-TB2 |
| Support/Tools | Available on Website |

Header

| | |
|----------|----------------------|
| 3D Model | Available on Website |
|----------|----------------------|

