



Representative

Catalog Number: HSC8-4
Product ID: 7TAA017170R0001
UPC Number: 78621087864
EAN Number: 05414363153054
Status: A

Heat-Shrinkable HSC Series End Caps for Cable Range 8 - 6 AWG, Expanded Diameter 0.51 inch, Length 2.5 inch, rated for 600 Volt, 90 degrees continuous use, Material: Cross-linked polyolefin with thermoplastic adhesive liner, Black

- Provides effective method for sealing cable ends, pipe conduit, etc. Extra thickness at the tip of the end prevents sharp ends of the cable from puncturing the seal.
- Resistant to common fluids and solvents.
- Adhesive liner provides complete environmental protection and insulation.

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Heavy-Wall Heat Shrinkable Tubing
Special Features	Provides effective method for sealing cable ends, pipe conduit, etc. Extra thickness at the tip of the end prevents sharp ends of the cable from puncturing the seal.
Voltage Rating	600 V
Length	2.5 in ; 63.5 mm
Flammability	Flame Retardant
Color	Black

European Specifications (ETIM)

ETIM	EC000218 Heat-shrink end cap
Inner diameter before heat-shrink	12.954mm
Inner diameter after heat-shrink	4.064mm
Total length after shrink	0.0635mm

Packaging

Inner Quantity	10
Inner Dimensions (inches)	5.6x3.55x1.4
Outer Quantity	100
Outer Dimensions (inches)	6.5x6.1x6.7
Weight Uom	1.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000470
Instruction Sheet	TA01621-TB2
Safety Data Sheet (SDS) Global	SDS-00046-TB2