



Catalog Number: FSCG-0382
Product ID: 7TCA303080R0074
UPC Number: 78621014527
EAN Number: 05415022418279
Status: A



Actual

Non Armoured Cable Gland for Food and Beverage, Thread Size 3/8 Inch NPT, Cable Range 5 to 10mm, Thread Length 7mm, Stainless Steel

- Smooth hygienic external casting
- One piece, fully enclosed
- Suitable for splash zones
- Corrosion resistant
- Splash zone and wash down areas
- Packaging and transfer areas
- Medical equipment - non contact
- Pharmaceutical, packaging and processing

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Non Armoured Cable Gland for Food and Beverage
Application	Food and Beverage Applications
Standard	NSF, RoHS, WEEE, LVD
Size	3/8 Inch NPT
Conductor Range	5 to 10 Millimeters
Material	Stainless Steel
Color	Metallic
Temperature Rating	-20 to +100 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/8 inch
Thread length	7mm
Suitable for cable diameter	5 - 10mm
Material	Metal
Material quality	Stainless steel V4A
Surface protection	Untreated
Degree of protection (IP)	IP68
Colour	Natural colour
Model	Straight
Operating temperature	-20-+100°C

Packaging

Inner Quantity	1
Inner Dimensions (inches)	1.5x1x1
Outer Quantity	5
Outer Dimensions (inches)	11.02x3.94x15.75
Weight Uom	22 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000034
Instruction Sheet	TA05287-TB2
Support/Tools	Available on Website

