



Representative

Catalog Number: HSC500
Product ID: 7TAA017190R0002
UPC Number: 78621089831
EAN Number: 05414363153030
Status: A

Heat-Shrinkable HSC Series End Caps for Cable Range 1500 - 2500 MCM, Expanded Diameter 4.7 inch, Length 5.5 inch, rated for 600 Volt, 90 degrees continuous use, Material: Cross-linked polyolefin with thermoplastic adhesive liner, Black

- Provides effective method for sealing cable ends, pipe conduit, etc. Extra thickness at the tip of the end prevents sharp ends of the cable from puncturing the seal.
- Resistant to common fluids and solvents.
- Adhesive liner provides complete environmental protection and insulation.

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Heavy-Wall Heat Shrinkable Tubing
Special Features	Provides effective method for sealing cable ends, pipe conduit, etc. Extra thickness at the tip of the end prevents sharp ends of the cable from puncturing the seal.
Voltage Rating	600 V
Length	5.5 in ; 139.7 mm
Flammability	Flame Retardant
Color	Black

European Specifications (ETIM)

ETIM	EC000218 Heat-shrink end cap
Inner diameter before heat-shrink	119.38mm
Inner diameter after heat-shrink	39.878mm
Total length after shrink	0.1397mm

Packaging

Inner Quantity	1
Outer Quantity	5
Outer Dimensions (inches)	13x6x13
Weight Uom	33.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000470
Instruction Sheet	TA01621-TB2
Safety Data Sheet (SDS) Global	SDS-00046-TB2