



Actual

**Catalog Number:** FSCG-0501  
**Product ID:** 7TCA303080R0075  
**UPC Number:** 78621014528  
**EAN Number:** 05415022418286  
**Status:** A

Non Armoured Cable Gland for Food and Beverage, Thread Size 1/2 Inch NPT, Cable Range 6 to 12mm, Thread Length 10mm, Stainless Steel

- Smooth hygienic external casting
- One piece, fully enclosed
- Suitable for splash zones
- Corrosion resistant
- Splash zone and wash down areas
- Packaging and transfer areas
- Medical equipment - non contact
- Pharmaceutical, packaging and processing

#### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Non Armoured Cable Gland for Food and Beverage
Application	Food and Beverage Applications
Standard	NSF, RoHS, WEEE, LVD
Size	1/2 Inch NPT
Conductor Range	6 to 12 Millimeters
Material	Stainless Steel
Color	Metallic
Temperature Rating	-20 to +100 C

#### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Thread length	10mm
Suitable for cable diameter	6 - 12mm
Material	Metal
Material quality	Stainless steel V4A
Surface protection	Untreated
Degree of protection (IP)	IP68
Colour	Natural colour
Model	Straight
Operating temperature	-20-+100°C

#### Packaging

Inner Quantity	1
Inner Dimensions (inches)	1.5x1x1
Outer Quantity	5
Outer Dimensions (inches)	11.02x3.94x15.75
Weight Uom	0.29 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000034
Instruction Sheet	TA05287-TB2
Support/Tools	Available on Website

