



Actual

Catalog Number: EXS04AMC2
Product ID: 7TCA297180R0092
UPC Number: 78621019503
EAN Number: 05011949230644
Status: A

Single Compression Cable Gland, 1/2 Inch NPT Thread, For Use with Non-Armoured Cable, Flameproof Ex d and Increased Safety Ex e, IP66-68 Rating, Length 40mm, Cable Range 4 to 12mm, Stainless Steel

North American Specifications (UNSPSC)

| | |
|--------------------------|--|
| UNSPSC | 39121431 Cable gland connector |
| IGCC | 4601 Cable gland connector |
| Type | Single Compression Cable Gland |
| Application | For Use with Unarmoured Cable to Provide Secure Cable Connections Through Knockouts and Threaded Entries |
| Standard | UL Listed, Approved to EN60079-0, 60079-1, 60079-7, 60079-31 |
| Size | 1/2 Inch NPT |
| Conductor Range | 4 to 12 Millimeters |
| Material | Stainless Steel |
| Color | Metallic |
| Insulation | IP66-68 Rating |
| Temperature Rating | -40 to 80 C |
| Environmental Conditions | Flameproof Ex d and Increased Safety Ex e |

European Specifications (ETIM)

| | |
|--|----------------------------|
| ETIM | EC000441 Cable screw gland |
| Thread type | NPT |
| Nominal thread size inch/gas pipe thread | 1/2 inch |
| Thread length | 16mm |
| Hexagon angular dimension | 24.5mm |
| Suitable for cable diameter | 4.0-12.0mm |
| Material | Metal |
| Material quality | Stainless steel V4A |
| Surface protection | Untreated |
| Halogen free | N |
| Glass-fibre reinforced | N |
| Degree of protection (IP) | IP68 |
| Shock resistant | N |
| Colour | Natural colour |
| Bend radius protection/trumpet flare | N |
| With locknut | N |
| Model | Straight |
| Flat cable coupling | N |
| Strain relief | N |
| Operating temperature | -40-+80°C |
| Explosion-tested version | Y |
| For Ex-zone gas | None |
| For Ex-Zone dust | None |
| EMC-version | N |

Packaging

| | |
|---------------------------|------------------|
| Inner Quantity | 2 |
| Inner Dimensions (inches) | 7.09x3.54x3.54 |
| Outer Quantity | 50 |
| Outer Dimensions (inches) | 3.94x15.75x11.02 |



Weight Uom

0.22 lbs. Each