



Representative

Catalog Number: NCG-1002G
Product ID: 7TCA303070R0200
UPC Number: 78621015346
EAN Number: 05415022425178
Status: Active

Non Armoured Cable Gland, Thread Size 1 Inch NPT, Cable Range 18 to 25 Millimeters, Thread Length 18 Millimeters, Nylon, Grey

- Low profile compact cable glands
- Wide cable clamping range
- Good corrosion resistance

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Non Armoured Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	UL514B, CSA, RoHS, WEEE, LVD
Size	1 Inch NPT
Conductor Range	18 to 25 Millimeters
Material	Nylon
Color	Gray
NEMA Rating	NEMA 4
Temperature Rating	-20 to +100 Degrees C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1 inch
Thread length	18mm
Suitable for cable diameter	18 - 25mm
Material	Plastic
Material quality	Polyamide (PA)
Halogen free	Y
Degree of protection (IP)	IP68
Colour	Dark grey
Model	Straight
Operating temperature	-20-+100°C

Packaging

Inner Quantity	5
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	20
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.01 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000030
Technical Drawing / Data Sheet Canada	TDS000030
Instruction Sheet	TA05283-TB2
Support/Tools	Available on Website
Video US	Available on Website

Thomas & Betts - USA