

Engineered-Performance Material Cable Ties

Resists acids, salts and bases.

Ty-Rap® Weather-Resistant Polypropylene Ties

- Excellent resistance to chemical exposure
- Greater UV resistance
- Buoyant – will float to the surface of most liquids

Color — Black

For use in temperatures ranging from
-40° F to 185° F (-40° C to 85° C)



BULK PKG. CAT. NO.	WIDTH IN./MM	BODY LENGTH IN./MM	MAX. WIRE BUNDLE DIA. IN./MM	TENSILE STR. LBS./N	BULK PKG. QTY.
TYP23MX	.09/2.29	3.62/91.95	.63/16.00	18/80.07	1,000
TYP25MX	.18/4.57	7.31/185.67	1.75/44.45	30/133.40	1,000
TYP28MX	.18/4.57	14.20/360.68	4.00/101.60	30/133.40	1,000
TYP27MX	.27/6.86	13.20/335.28	3.50/88.90	60/266.90	500

Long life in UV and chemical environments.

Ty-Rap® Weather-Resistant Nylon 12 Ties

This material provides very good resistance to ultraviolet light and chemical exposure. Nylon 12 is a lower, moisture-absorbing material than 6.6 nylon, and the effect of water on properties is much less.

For use in temperatures ranging from
-40° F to 185° F (-40° C to 85° C).

Color — Black



STD. CAT. NO.	BULK CAT. NO.	BODY WIDTH IN./MM	LENGTH IN./MM	MAX. WIRE BUNDLE DIA. IN./MM	TENSILE STRENGTH LBS./N	STD. PKG. QTY.	BULK PKG. QTY.
TYC525MX	TYC25MX	.18/4.57	7.31/185.67	1.75/44.45	35/155.70	100	1,000
—	TYC28MX	.18/4.57	14.20/360.68	4.00/101.60	35/155.70	—	1,000
—	TYC272MX	.27/6.86	8.00/203.20	2.00/50.80	85/378.10	—	500
TYC527MX	TYC27MX	.27/6.86	13.20/335.28	3.50/88.90	85/378.10	50	500
—	TYC29MX	.30/7.62	30.00/762.00	9.00/228.60	85/378.10	—	500