



**Catalog Number:** TYS12-470C  
**Product ID:** 7TAG009450R0202  
**UPC Number:** 78621091540  
**EAN Number:** 05414363067825  
**Status:** A



Multi-Lok 316 Stainless Steel Cable Tie, Black Nylon 11 Coated for High Temperature Applications, Weather and Ultraviolet Resistant, Length of 300mm (11.8 Inches), Width of 12mm (0.47 Inch), Thickness of 0.4mm (0.02 Inch), Tensile Strength Rating of 1112 Newtons (250 Pounds)

- Application Tools: WTAE200, WTAE201,

Actual



**North American Specifications (UNSPSC)**

UNSPSC	39121703 Cable ties
IGCC	5046 Stainless Steel Ties
Type	Stainless Steel
Standard	UL E49405
Width	0.47 in ; 12 mm
Length	11.8 in ; 300 mm
Thickness	0.02 in ; 0.4 mm
Bundle Diameter	Max 3.2 in ; Max 80 mm
Material	316 Stainless Steel
Color	Black
Lock Mechanism	Multi-Lok
Tensile Strength	250 pounds ; 1112 newtons

Actual

**European Specifications (ETIM)**

ETIM	EC000046 Cable tie
Band width	12mm
Length belt/tape/tie	300mm
Tie thickness	0.4mm
Max. bundle diameter	80mm
Min. holding force	890N
Operating temperature	-40-+150°C
Model	Internal toothing
Band closure	Ball latch
Material	Metal
Material quality	Stainless steel 316 (V4A)
Surface protection	Plastic-coated
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y

**Packaging**

Inner Quantity	100
Outer Quantity	1000
Outer Dimensions (inches)	17x7x6.5
Weight Uom	2.13 lbs. per 100

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000433
--------------------------------	-----------

