



Actual

**Catalog Number:** **ISR100-102**  
**Product ID:** 7TBA297190R0003  
**UPC Number:** 78621005946  
**EAN Number:** 05011949235793  
**Status:** A

Industrial Strain-Relief Fitting, Hub Size 1 Inch NPT, Cable Range 19.94 to 26.04mm, CSA and UL Listed, Outer Diameter 48.26mm, Aluminum

- For use with unarmoured cable types suitable for use in Class I, Zone 1
- Tray Cable complies with IEC requirements when used with enclosures containing no arcing or sparking devices.
- Portable Cord complies with IEC requirements when used with enclosures containing no arcing or sparking devices

#### North American Specifications (UNSPSC)

UNSPSC	39121719 Strain reliefs
IGCC	5067 Strain reliefs
Type	Industrial Strain Relief Fitting
Special Features	100% of IEC Cable Pull-Out Requirements with No External Clamping
Application	Connection and Strain Relief for Conduit Systems
Standard	CSA, UL E328651 and E311979
Cable Size	19.94 to 26.04 mm
Hub Size	1 in
Material	Aluminum
Color	Metallic

#### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Other
Operating temperature	-50-+110°C

#### Packaging

Outer Quantity	10
Outer Dimensions (inches)	5.94x5.94x4.69
Weight Uom	23.5 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001684
Catalog Page	Available on Website
Support/Tools	Available on Website