



Actual

Catalog Number: BCG-M202-L
Product ID: 7TCA303030R0012
UPC Number: 78621015644
EAN Number: 05415022427523
Status: Active

Non Armoured Cable Gland, Thread Size M20, Cable Range 6 to 12 Millimeters, Thread Length 12 Millimeters, Nickel Plated Brass

- Low profile compact cable glands
- Wide cable clamping range
- Good corrosion resistance

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Non Armoured Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	cULus, RoHS, WEEE, LVD
Size	M20
Conductor Range	6 to 12 Millimeters
Material	Brass
Finish	Nickel plated
Color	Metallic
NEMA Rating	NEMA 4
Temperature Rating	-20 to +100 Degrees C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	Metric
Nominal thread size metric/PG	20
Pitch thread	1.5mm
Thread length	12mm
Suitable for cable diameter	6 - 12mm
Material	Metal
Material quality	Brass
Surface protection	Nickel-plated
Degree of protection (IP)	IP68
Colour	Natural colour
Model	Straight
Operating temperature	-20-+100°C

Packaging

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	50
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.02 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000028
Technical Drawing / Data Sheet Canada	TDS000028
Instruction Sheet	TA05283-TB2
Support/Tools	Available on Website

Thomas & Betts - USA