



Actual



Actual

Catalog Number: 257
Product ID: 7TAA106060R0002
UPC Number: 78621000257
Status: A

Squeeze Connector, Straight, Trade Size 1-1/4 Inch, Knockout Size 1-1/4 Inch, Cable Range 1.500 to 1.656 Inch, Malleable Iron

North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	T&B Squeeze Connectors Will Fit Every Size of Armored Cable, Leaded Cable and Flexible Conduit
Application	For Use with Armored Cable and Flexible Metal Conduit
Standard	UL E23018, CSA 2884
Size	1-1/4 Inch
Conductor Range	1.500 to 1.656 Inch
Material	Malleable Iron
Finish	Zinc Plated
Color	Metallic
Insulation	No

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/4 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Thread length	13.49mm
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Inner Quantity	5
Inner Dimensions (inches)	4.5x5x3
Outer Quantity	10
Outer Dimensions (inches)	9x5.5x7
Weight Uom	52 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website