



**NOTES:**

1. FITTING CONNECTION TYPE : Press x Press
2. PIPE SIZE - PIPE FITTING : 1-1/4" x 1-1/4"
3. TUBE FITTING MATERIAL : Carbon Steel
4. MAX. PRESSURE : 200 psi
5. TEMP. RANGE : 0° to 250° F

|                                                                                                                                                                                                                                         |                                                                                                                                                                                                                                                                                                                                                                                                                                                           |                                                                                                                                                                                                            |  |                                                                   |  |       |  |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------|--|-------|--|
| 5. TEMP: RANGE : 0° to 250° F                                                                                                                                                                                                           |                                                                                                                                                                                                                                                                                                                                                                                                                                                           | COMPONENT                                                                                                                                                                                                  |  | Extended Coupling No Stop                                         |  |       |  |
| <div><p>100 Grainger Parkway, Lake Forest, Illinois 60045-5201<br/>1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000<br/>www.grainger.com</p></div> | <p>This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications.</p> <p>You are solely responsible for the use of the file, information or specifications.</p> | <p>This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.</p> |  | <div>49ET72</div> <p>MegaPress extended coupling, 1.25"x1.25"</p> |  | UNIT  |  |
|                                                                                                                                                                                                                                         |                                                                                                                                                                                                                                                                                                                                                                                                                                                           |                                                                                                                                                                                                            |  |                                                                   |  | INCH  |  |
|                                                                                                                                                                                                                                         |                                                                                                                                                                                                                                                                                                                                                                                                                                                           |                                                                                                                                                                                                            |  |                                                                   |  | SHEET |  |
|                                                                                                                                                                                                                                         |                                                                                                                                                                                                                                                                                                                                                                                                                                                           | SCALE                                                                                                                                                                                                      |  | 0.80                                                              |  |       |  |
|                                                                                                                                                                                                                                         |                                                                                                                                                                                                                                                                                                                                                                                                                                                           |                                                                                                                                                                                                            |  |                                                                   |  |       |  |