

Optio™ Cookware



Optio™ stainless steel cookware is specifically designed for the value conscious chef. Constructed of stainless steel and featuring an aluminum-clad bottom for quick and even heat distribution, all Optio™ Cookware is Induction ready.

Optio™ Natural Finish Fry Pans

ITEM	TOP DIA CM	BOTTOM DIA CM	HEIGHT CM	GAUGE	CASE LOT	COVER ITEM
3808	20.3	14.6	3.8	21	6	3908C
3809	24.1	19.4	4.4	21	6	3910C
3811	27.9	24.8	5.1	21	2	3911C
3812	31.8	27.6	5.7	21	2	3912C



Optio™ Non-Stick Fry Pans

ITEM	TOP DIA CM	BOTTOM DIA CM	HEIGHT CM	GAUGE	CASE LOT	COVER ITEM
N3817	17.8	12.1	4.4	21	6	3907C
N3808	20.3	14.6	3.8	21	6	3908C
N3809	24.1	19.4	4.4	21	6	3910C
N3811	27.9	24.8	5.1	21	2	3911C
N3812	31.8	27.6	5.7	21	2	3912C



N3809

Optio™ Sauté Pans

ITEM	CAPACITY L	DIAMETER CM	DEPTH CM	GAUGE	CASE LOT	COVER ITEM
3801	2.4	20.3	7.6	21	2	3908C
3804	3.8	24.1	10.8	21	2	3910C
3807	5.7	27.9	8.9	21	2	3911C



3804

Optio™ Sauce Pans

Sauce pans ship complete with domed cover

ITEM	CAPACITY L	DIAMETER CM	DEPTH CM	GAUGE	CASE LOT	COVER ITEM
3800	.9	14.0	7.0	21	6	3900C
3802	2.6	17.8	10.5	21	6	3907C
3803	3.8	20.3	12.1	21	6	3908C
3806	6.4	24.1	16.2	21	6	3910C
3813	9.9	27.9	17.8	21	6	3911C



3803