


# Wear-Ever® Aluminum Fry Pans



## VOTED BEST IN CLASS FOR 13 YEARS RUNNING

- Designed and built in the USA from extra-dent- and warp-resistant 3004 aluminum alloy
- Built for use in demanding commercial kitchens
- Available in natural finish or the best nonstick coatings in the industry, all made without PFOA – PowerCoat2™ (good), SteelCoat x3™ (better), and CeramiGuard® II (best)
- Fry pans are available in three handle styles – silicone Cool Handle®, TriVent® silicone handle, and TriVent plated handle
- Available with two silicone handle options rated at 450°F (232°C) for continuous use or 600°F (315°C) for intermittent use
- Replacement sleeves for Cool Handle and TriVent silicone-bonded handles restore handle comfort and performance to these hard-working pans
- Flat and domed covers are available



HANDLE	TOP DIA: IN (CM)	BOTTOM DIA: IN (CM)	HEIGHT: IN (CM)	GAUGE	CERAMIGUARD II ITEM #	STEELCOAT X3™ ITEM #	POWERCOAT2 ITEM #	NATURAL ITEM #	CASE LOT	FLAT COVER	DOMED COVER
Cool Handle	7 (17.8)	4¾ (12)	1½ (3.8)	8	Z4007	T4007	S4007	4007	6	67327	67427
Cool Handle	8 (20.3)	5¾ (14)	1¾ (4.8)	10	Z4008	T4008	S4008	4008	6	67312	67412
Cool Handle	10 (25.4)	7¾ (20)	2 (5.1)	8	Z4010	T4010	S4010	4010	6	67509	67409
Cool Handle	12 (30.5)	9¾ (25)	2¼ (5.7)	8	Z4012	T4012	S4012	4012	2	67521	67421
Cool Handle	14 (35.6)	10¾ (28)	2½ (6.4)	6	Z4014	T4014	S4014	4014	2	67541	67441
Silicone TriVent	7 (17.8)	4¾ (12)	1½ (3.8)	8	67927	67607	67807	67907	6	67327	67427
Silicone TriVent	8 (20.3)	5¾ (14)	1¾ (4.8)	10	67928	67608	67808	67908	6	67312	67412
Silicone TriVent	10 (25.4)	7¾ (20)	2 (5.1)	8	67930	67610	67810	67910	6	67509	67409
Silicone TriVent	12 (30.5)	9¾ (25)	2¼ (5.7)	8	67932	67612	67812	67912	2	67521	67421
Silicone TriVent	14 (35.6)	10¾ (28)	2½ (6.4)	6	67934	67614	67814	67914	2	67541	67441
Plated TriVent	7 (17.8)	4¾ (12)	1½ (3.8)	8	67947	67627	67007	67107	6	67327	67427
Plated TriVent	8 (20.3)	5¾ (14)	1¾ (4.8)	10	67948	67628	67008	67108	6	67312	67412
Plated TriVent	10 (25.4)	7¾ (20)	2 (5.1)	8	67950	67630	67010	67110	6	67509	67409
Plated TriVent	12 (30.5)	9¾ (25)	2¼ (5.7)	8	67952	67632	67012	67112	2	67521	67421
Plated TriVent	14 (35.6)	10¾ (28)	2½ (6.4)	6	67954	67634	67014	67114	2	67541	67441
<b>PURPLE ALLERGEN HANDLES</b>											
Purple allergen handle	7 (17.8)	4¾ (12)	1½ (3.8)	8	—	T400780	—	400780	6	67327	67427
Purple allergen handle	8 (20.3)	5¾ (14)	1¾ (4.8)	10	—	T400880	—	400880	6	67312	67412
Purple allergen handle	10 (25.4)	7¾ (20)	2 (5.1)	8	—	T401080	—	401080	6	67509	67409
Purple allergen handle	12 (30.5)	9¾ (25)	2¼ (5.7)	8	—	T401280	—	401280	2	67521	67421
Purple allergen handle	14 (35.6)	10¾ (28)	2½ (6.4)	6	—	T401480	—	401480	2	67541	67441



— watch it on [VOLLRATH.com/rivet](http://VOLLRATH.com/rivet) —

The **EXTREME HEAT** Test

00:24 MIN SEC

Vollrath 10" Aluminum Fry Pan with EverTite™ Rivets

See how Ever-Tite™ rivets stand up to 450° heat in the extreme heat test video at [VOLLRATH.com/rivet](http://VOLLRATH.com/rivet).