



Dealers Industrial Equipment

No.:

Date: 12-SEP-2016

DATA SHEET

Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : W22 Super Premium

Frame : 143/5T
Output : 1.5 HP
Frequency : 60 Hz
Poles : 2
Full load speed : 3485 rpm
Slip : 3.19 %
Voltage : 208-230/460 V
Rated current : 4.25-3.84/1.92 A
Locked rotor current : 32.3/16.1 A
Locked rotor current (I_L/I_n) : 8.4
No-load current : 1.80/0.900 A
Full load torque : 2.23 lb.ft
Locked rotor torque : 300 %
Breakdown torque : 350 %
Design : A
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 29 s (hot)
Service factor : 1.25
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000 m
Degree of Protection : IP55
Approximate weight : 42 lb
Moment of inertia : 0.04699 sq.ft.lb
Noise level : 68 dB(A)

	D.E.	N.D.E.
Bearings	6205 ZZ	6204 ZZ
Regreasing interval	---	---
Grease amount	---	---

Load	Power factor	Efficiency (%)
100%	0.83	86.5
75%	0.78	85.5
50%	0.67	84.0

Notes:

Downloaded from <http://dealersselectric.com>
Generated for Model #00156EG3E143T-W22

Performed by

Checked