



Dealers Industrial Equipment

No.:

Date: 12-SEP-2016

DATA SHEET

Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : W22 Super Premium

Frame : 143/5T
Output : 2 HP
Frequency : 60 Hz
Poles : 2
Full load speed : 3490 rpm
Slip : 3.06 %
Voltage : 208-230/460 V
Rated current : 5.66-5.12/2.56 A
Locked rotor current : 42.0/21.0 A
Locked rotor current (I_L/I_N) : 8.2
No-load current : 2.20/1.10 A
Full load torque : 2.97 lb.ft
Locked rotor torque : 320 %
Breakdown torque : 360 %
Design : A
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 23 s (hot)
Service factor : 1.25
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000 m
Degree of Protection : IP55
Approximate weight : 51 lb
Moment of inertia : 0.06099 sq.ft.lb
Noise level : 68 dB(A)

	D.E.	N.D.E.
Bearings	6205 ZZ	6204 ZZ
Regreasing interval	---	---
Grease amount	---	---

Load	Power factor	Efficiency (%)
100%	0.84	87.5
75%	0.80	87.5
50%	0.69	85.5

Notes:

Downloaded from <http://dealerselectric.com>
Generated for Model #00236EG3E145T-W22

Performed by

Checked