



Dealers Industrial Equipment

No.:

Date: 13-SEP-2016

DATA SHEET

Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : Three-Phase : Explosion Proof - NEMA Premium

Frame : 284T
Output : 10 HP
Frequency : 60 Hz
Poles : 8
Full load speed : 880 rpm
Slip : 2.22 %
Voltage : 208-230/460 V
Rated current : 29.4-26.6/13.3 A
Locked rotor current : 160/79.8 A
Locked rotor current (I_L/I_N) : 6.0
No-load current : 12.0/6.00 A
Full load torque : 58.9 lb.ft
Locked rotor torque : 250 %
Breakdown torque : 240 %
Design : B
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 30 s (hot)
Service factor : 1.15
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000 m
Degree of Protection : IP55
Approximate weight : 467 lb
Moment of inertia : 7.1992 sq.ft.lb
Noise level : 54 dB(A)

	D.E.	N.D.E.
Bearings	6311 2RS-C3	6211 2RS-C3
Regreasing interval	---	---
Grease amount	---	---

Load	Power factor	Efficiency (%)
100%	0.78	91.0
75%	0.73	91.7
50%	0.62	91.0

Notes:

Downloaded from <http://dealerselectric.com>
Generated for Model #01009XT3E284T

Performed by

Checked