



Dealers Industrial Equipment

No.:

Date: 23-SEP-2016

DATA SHEET

Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : W22 Super Premium

Frame : 254/6T
Output : 15 HP
Frequency : 60 Hz
Poles : 2
Full load speed : 3545 rpm
Slip : 1.53 %
Voltage : 208-230/460 V
Rated current : 38.5-34.8/17.4 A
Locked rotor current : 268/134 A
Locked rotor current (I_L/I_n) : 7.7
No-load current : 14.0/7.00 A
Full load torque : 21.9 lb.ft
Locked rotor torque : 270 %
Breakdown torque : 350 %
Design : A
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 28 s (hot)
Service factor : 1.25
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000 m
Degree of Protection : IP55
Approximate weight : 273 lb
Moment of inertia : 1.5610 sq.ft.lb
Noise level : 72 dB(A)

	D.E.	N.D.E.
Bearings	6309 C3	6209 C3
Regreasing interval	19000 h	20000 h
Grease amount	13 g	9 g

Load	Power factor	Efficiency (%)
100%	0.86	92.4
75%	0.82	91.7
50%	0.72	90.2

Notes:

Downloaded from <http://dealersselectric.com>
Generated for Model #01536EG3E254T-W22

Performed by

Checked