



Dealers Industrial Equipment

No.:

Date: 23-SEP-2016

DATA SHEET

Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : Three-Phase : Explosion Proof - NEMA Premium

Frame : 254T
Output : 15 HP
Frequency : 60 Hz
Poles : 2
Full load speed : 3540 rpm
Slip : 1.67 %
Voltage : 575 V
Rated current : 13.9 A
Locked rotor current : 94.7 A
Locked rotor current (I_L/I_n) : 6.8
No-load current : 4.48 A
Full load torque : 22.0 lb.ft
Locked rotor torque : 200 %
Breakdown torque : 270 %
Design : B
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 31 s (hot)
Service factor : 1.15
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000 m
Degree of Protection : IP55
Approximate weight : 318 lb
Moment of inertia : 1.1863 sq.ft.lb
Noise level : 75 dB(A)

	D.E.	N.D.E.
Bearings	6309 2RS-C3	6209 2RS-C3
Regreasing interval	---	---
Grease amount	---	---

Load	Power factor	Efficiency (%)
100%	0.87	91.0
75%	0.83	90.5
50%	0.74	90.0

Notes:

Downloaded from <http://dealerselectric.com>
Generated for Model #01536XT3H254T

Performed by

Checked