



Dealers Industrial Equipment

No.:

Date: 23-SEP-2016

DATA SHEET

Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : W22 Super Premium

Frame : 364/5T
Output : 50 HP
Frequency : 60 Hz
Poles : 6
Full load speed : 1185 rpm
Slip : 1.25 %
Voltage : 208-230/460 V
Rated current : 133-121/60.3 A
Locked rotor current : 1030/513 A
Locked rotor current (I_L/I_N) : 8.5
No-load current : 62.0/31.0 A
Full load torque : 219 lb.ft
Locked rotor torque : 260 %
Breakdown torque : 330 %
Design : A
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 12 s (hot)
Service factor : 1.25
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000 m
Degree of Protection : IP55
Approximate weight : 895 lb
Moment of inertia : 25.037 sq.ft.lb
Noise level : 66 dB(A)

	D.E.	N.D.E.
Bearings	6314 C3	6314 C3
Regreasing interval	17000 h	17000 h
Grease amount	27 g	27 g

Load	Power factor	Efficiency (%)
100%	0.81	95.0
75%	0.75	94.5
50%	0.63	93.6

Notes:

Downloaded from <http://dealerselectric.com>
Generated for Model #05012EG3E365T-W22

Performed by

Checked