



Dealers Industrial Equipment

No.:

Date: 27-SEP-2016

DATA SHEET

Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : Three-Phase : Explosion Proof - NEMA Premium

Frame : 404/5T
Output : 60 HP
Frequency : 60 Hz
Poles : 6
Full load speed : 1185 rpm
Slip : 1.25 %
Voltage : 575 V
Rated current : 56.2 A
Locked rotor current : 388 A
Locked rotor current (I_L/I_n) : 6.9
No-load current : 20.0 A
Full load torque : 262 lb.ft
Locked rotor torque : 250 %
Breakdown torque : 270 %
Design : B
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 29 s (hot)
Service factor : 1.15
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000 m
Degree of Protection : IP55
Approximate weight : 1213 lb
Moment of inertia : 36.858 sq.ft.lb
Noise level : 65 dB(A)

	D.E.	N.D.E.
Bearings	6217 C3	6314 C3
Regreasing interval	13507 h	14267 h
Grease amount	21 g	27 g

Load	Power factor	Efficiency (%)
100%	0.85	94.5
75%	0.82	94.5
50%	0.73	93.6

Notes:

Downloaded from <http://dealerselectric.com>
Generated for Model #06012XT3H404T

Performed by

Checked