

DATA SHEET



Three Phase Induction Motor - Squirrel Cage

Customer : Dealers Industrial Equipment 800-469-3110
Customer reference : 06018OP3HFP364TS-W40

Product line : W40 High Efficiency Three-Phase Product code : 14281212
Catalog # : 06018OP3HFP364TS-W40

Frame	: 364/5TS	Locked rotor time	: 39s (cold) 22s (hot)
Output	: 60 HP (45 kW)	Temperature rise	: 80 K
Poles	: 4	Duty cycle	: Cont.(S1)
Frequency	: 60 Hz	Ambient temperature	: -20°C to +40°C
Rated voltage	: 575 V	Altitude	: 1000 m.a.s.l.
Rated current	: 56.8 A	Protection degree	: IP23
L. R. Amperes	: 346 A	Cooling method	: IC01 - ODP
LRC	: 6.1x(Code G)	Mounting	: F-1
No load current	: 18.4 A	Rotation ¹	: Both (CW and CCW)
Rated speed	: 1777 rpm	Starting method	: Direct On Line
Slip	: 1.28 %	Approx. weight ³	: 723 lb
Rated torque	: 175 ft.lb		
Locked rotor torque	: 180 %		
Breakdown torque	: 229 %		
Insulation class	: F		
Service factor	: 1.15		
Moment of inertia (J)	: 12.8 sq.ft.lb		
Design	: B		

Output	50%	75%	100%	Foundation loads	
Efficiency (%)	93.0	93.6	93.6	Max. traction	: 1036 lb
Power Factor	0.73	0.82	0.85	Max. compression	: 1759 lb

	Drive end	Non drive end
Bearing type	: 6314 C3	: 6212 Z C3
Sealing	: Without Bearing Seal	: Without Bearing Seal
Lubrication interval	: 20000 h	: 20000 h
Lubricant amount	: 27 g	: 13 g
Lubricant type	Mobil Polyrex EM	

Notes
downloaded from <http://dealerselectric.com>

This revision replaces and cancel the previous one, which must be eliminated.
(1) Looking the motor from the shaft end.
(2) Measured at 1m and with tolerance of +3dB(A).
(3) Approximate weight subject to changes after manufacturing process.
(4) At 100% of full load.

These are average values based on tests with sinusoidal power supply, subject to the tolerances stipulated in NEMA MG-1.

Rev.	Changes Summary	Performed	Checked	Date
Performed by				
Checked by				
Date	14/04/2019			

Page 1 / 2
Revision


LOAD PERFORMANCE CURVE

Three Phase Induction Motor - Squirrel Cage



Customer : Dealers Industrial Equipment 800-469-3110
Customer reference : 06018OP3HFP364TS-W40

Product line : W40 High Efficiency Three-Phase Product code : 14281212
Catalog # : 06018OP3HFP364TS-W40



Performance : 575 V 60 Hz 4P

Rated current	: 56.8 A	Moment of inertia (J)	: 12.8 sq.ft.lb
LRC	: 6.1	Duty cycle	: Cont.(S1)
Rated torque	: 175 ft.lb	Insulation class	: F
Locked rotor torque	: 180 %	Service factor	: 1.15
Breakdown torque	: 229 %	Temperature rise	: 80 K
Rated speed	: 1777 rpm	Design	: B

Rev.	Changes Summary		Performed	Checked	Date
Performed by		Page 2 / 2Revision			
Checked by					
Date	14/04/2019				

