



Dealers Industrial Equipment

No.:

Date: 29-SEP-2016

DATA SHEET Single-phase induction motor - Squirrel cage rotor

Customer :
 Product line : Pool & Spa Motors : C-Face - Start Capacitor - High Service Factor

Frame : M56J
 Output : 1.5 HP
 Frequency : 60 Hz
 Poles : 2
 Full load speed : 3500 rpm
 Slip : 2.78 %
 Voltage : 230 V
 Rated current : 7.50 A
 Locked rotor current : 55.5 A
 Locked rotor current (I_L/I_n) : 7.4
 No-load current : 3.90 A
 Full load torque : 2.22 lb.ft
 Locked rotor torque : 180 %
 Breakdown torque : 310 %
 Design : ---
 Insulation class : B
 Temperature rise : 80 K
 Locked rotor time : 6 s (hot)
 Service factor : 1.30
 Duty cycle : S1
 Ambient temperature : -20°C - +50°C
 Altitude : 1000 m
 Degree of Protection : IP21
 Approximate weight : 34 lb
 Moment of inertia : 0.04034 sq.ft.lb
 Noise level : ---

	D.E.	N.D.E.
Bearings	6203 2RS	6203 ZZ
Regreasing interval	---	---
Grease amount	---	---

Load	Power factor	Efficiency (%)
100%	0.85	76.3
75%	0.80	72.0
50%	0.72	63.5

Notes:
 Downloaded from <http://dealerselectric.com>
 Generated for Model #PCJ115H

Performed by

Checked