



Dealers Industrial Equipment

No.:

Date: 29-SEP-2016

DATA SHEET Single-phase induction motor - Squirrel cage rotor

Customer :
Product line : Pool & Spa Motors : Square Flange - Start Capacitor - Low Service Factor

Frame : K48Y
Output : 0.75 HP
Frequency : 60 Hz
Poles : 2
Full load speed : 3465 rpm
Slip : 3.75 %
Voltage : 115/230 V
Rated current : 10.2/5.10 A
Locked rotor current : 54.1/27.0 A
Locked rotor current (I_L/I_n) : 5.3
No-load current : 7.70/3.85 A
Full load torque : 1.12 lb.ft
Locked rotor torque : 140 %
Breakdown torque : 260 %
Design : ---
Insulation class : B
Temperature rise : 80 K
Locked rotor time : 6 s (hot)
Service factor : 1.30
Duty cycle : S1
Ambient temperature : -20°C - +50°C
Altitude : 1000 m
Degree of Protection : IP21
Approximate weight : 24 lb
Moment of inertia : 0.02326 sq.ft.lb
Noise level : ---

	D.E.	N.D.E.	Load	Power factor	Efficiency (%)
Bearings	6203 2RS	6203 ZZ	100%	0.72	66.2
Regreasing interval	---	---	75%	0.63	62.5
Grease amount	---	---	50%	0.53	55.0

Notes:
Downloaded from <http://dealerselectric.com>
Generated for Model #PCQ107

Performed by

Checked