

# WERMA Signal Devices

## Visual 57/58mm Bracket Mount Beacons

### Features

- Choose from permanent incandescent, permanent LED, or flashing Xenon models
- Bracket mount installation
- 57 and 58mm diameters
- Light-intensive Xenon flash in flash models
- Bulb not included with incandescent models
- 2-year warranty



### Visual 57/58mm Bracket Mount Beacons 203, 204, and 205 Series Selection Chart

Part Number	Price	Color	Drawing Link	Description	Voltage	Current	Starting Current	Operating Temp /Protection	Life Duration	Housing Material	Weight g [oz]	Connection	Agency Approvals
<b>25.8 mm (Bracket Mount)</b>													
<a href="#">20310000</a>	\$21.50	Red	<a href="#">PDF</a>	Incandescent Permanent Light 57mm	12-240V AC/ DC max (depends on bulb selection; bulb sold separately)	Depends on bulb selection. (bulb sold separately)	-		up to 5,000h		55 [1.94]		
<a href="#">20320000</a>	\$21.50	Green	<a href="#">PDF</a>										
<a href="#">20330000</a>	\$21.50	Yellow	<a href="#">PDF</a>										
<a href="#">20340000</a>	\$21.50	Clear	<a href="#">PDF</a>										
<a href="#">20350000</a>	\$21.50	Blue	<a href="#">PDF</a>	LED Permanent Light 58mm	115VAC	< 25mA	≤ 0.5 A	-4 to 122°F [-20 to 50°C]	up to 100,000h	Polycarbonate cap Polyamide base	72 [2.53]	2.5 mm² Screwless CAGE CLAMP® - technology (18-14 AWG)  Cable gland: m12 x1.5 Cable diameter: 3-6 mm	cULus file E164155, CE, RoHS
<a href="#">20410067</a>	\$89.00	Red	<a href="#">PDF</a>										
<a href="#">20420067</a>	\$89.00	Green	<a href="#">PDF</a>										
<a href="#">20430067</a>	\$89.00	Yellow	<a href="#">PDF</a>										
<a href="#">20440067</a>	\$133.00	Clear	<a href="#">PDF</a>										
<a href="#">20450067</a>	\$133.00	Blue	<a href="#">PDF</a>										
<a href="#">20410075</a>	\$73.00	Red	<a href="#">PDF</a>		24V AC/DC	< 45mA		IP65					
<a href="#">20420075</a>	\$73.00	Green	<a href="#">PDF</a>										
<a href="#">20430075</a>	\$73.00	Yellow	<a href="#">PDF</a>										
<a href="#">20440075</a>	\$119.00	Clear	<a href="#">PDF</a>										
<a href="#">20450075</a>	\$119.00	Blue	<a href="#">PDF</a>										
<a href="#">20510055</a>	\$106.00	Red	<a href="#">PDF</a>										
<a href="#">20520055</a>	\$110.00	Green	<a href="#">PDF</a>										
<a href="#">20530055</a>	\$104.00	Yellow	<a href="#">PDF</a>										
<a href="#">20540055</a>	\$110.00	Clear	<a href="#">PDF</a>										
<a href="#">20550055</a>	\$110.00	Blue	<a href="#">PDF</a>										
<a href="#">20510067</a>	\$106.00	Red	<a href="#">PDF</a>	115VAC	< 20mA								
<a href="#">20520067</a>	\$110.00	Green	<a href="#">PDF</a>										
<a href="#">20530067</a>	\$104.00	Yellow	<a href="#">PDF</a>										
<a href="#">20540067</a>	\$110.00	Clear	<a href="#">PDF</a>										
<a href="#">20550067</a>	\$110.00	Blue	<a href="#">PDF</a>										

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

### Bulbs



Bulbs for Incandescent Permanent Visual Element					
Part Number	Price	Description	Wattage	Voltage	Life Duration
<a href="#">95584035</a>	\$8.25	Bulb for Incandescent Light BA15d Bayonet Socket	5W	24VDC	up to 5,000h
<a href="#">95584038</a>	\$8.25			230VAC	
<a href="#">95584057</a>	\$8.25			115VAC	



# Signal Devices

## Beacon Accessories

WERMA Beacons Accessories						
Part Number	Price	Drawing Link	Description	Operating Temp.	Material	Weight
<b>Installation Beacon Accessories</b>						
<a href="#">97581201</a>	\$14.50	<a href="#">PDF</a>	WERMA tube adapter, tube mount, 57mm diameter, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.	-4 to 122°F [-20 to 50°C]	Polyamide / Fiberglass	1.13 g [0.04 oz]
<a href="#">97581202</a>	\$14.00	<a href="#">PDF</a>	WERMA surface mounting base, base mount, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.		Polyamide / Fiberglass with rubber seal	2.83 g [0.1 oz]
<a href="#">97581503</a>	\$44.00	<a href="#">PDF</a>	WERMA beacon enclosure, surface mount, 1 hole. For use with beacons with 37mm (PG 29) mounting installation.		Polycarbonate/ABS blend	8.5 g [0.3 oz]
<a href="#">97581507</a>	\$61.00	<a href="#">PDF</a>	WERMA beacon enclosure, surface mount, 2 holes. For use with beacons with 37mm (PG 29) mounting installation.			14.17 g [0.5 oz]
<a href="#">97581508</a>	\$80.00	<a href="#">PDF</a>	WERMA beacon enclosure, surface mount, 3 holes. For use with beacons with 37mm (PG 29) mounting installation.			17g [0.6 oz]
<a href="#">97581522</a>	\$5.75	<a href="#">PDF</a>	WERMA anti-twist washer, stainless steel. For use with Werma beacons with 37mm (PG 29) mounting installation.		304 Stainless steel	0.57 g [0.02 oz]
<b>Freestanding Beacon Accessories</b>						
<a href="#">9600001</a>	\$17.00	<a href="#">PDF</a>	WERMA mounting bracket, tube mount, black, polyamide. For use with 50mm or 70mm terminal elements. M16 x 1.5mm cable gland included.	-4 to 122°F [-20 to 50°C]	Polyamide	57g [2.01 oz]
<a href="#">97520901</a>	\$20.50	<a href="#">PDF</a>	WERMA plastic base with integrated tube, base mount, 70mm diameter, 110mm length, black, polyamide. For use with 209 or 219 series beacons.		Polyamide	0.1 lbs [1.6 oz]
<a href="#">97520902</a>	\$5.75	<a href="#">PDF</a>	WERMA cable gland, M25 x 1.5mm thread type, polyamide, black, accepts 8 to 17mm diameter cable, IP68.		Nylon	0.1 lbs [1.6 oz]
<a href="#">97582603</a>	\$43.00	<a href="#">PDF</a>	WERMA galvanized wire guard, steel. For use with 826, 827, 828 or 829 series industrial signal beacons.		Wire D 3mm, chromed	140g [4.93 oz]
<a href="#">97582605</a>	\$10.00	<a href="#">PDF</a>	WERMA mounting bracket, wall mount, black, ABS/PC plastic. For use with 826, 827, 828 and 829 series industrial signal beacons.		Polycarbonate/ABS blend	62g [2.19 oz]

