



1250 Welsh Rd

North Wales, PA 19454

Phone: 800.445.5681 • Fax: 800.346.5511

Email: [info@wescomfg.com](mailto:info@wescomfg.com)

## PART NO. 240005, 30BT STANDARD SERIES DRUM TRUCK



- Heavy duty, double-welded joints, 1" structural pipe frame.
- Handles 30, 55 and 85 gallon steel, poly or fiber drum, according to model.
- Self standing or with kick stand for upright storage.
- Multi-functional drum truck allows you to move drums on four wheels and acts as a drum cradle for storage or disposal.
- 16.5" drain height.
- With two wheels resting on floor, 28" to bottom of lowered chime hook.
- Steel drums only.
- Handles 30 & 55 gal. drums.

[Video](#) | [Specifications](#)

### Video



### Specifications



<b>PART NUMBER</b>	240005
<b>MODEL</b>	30BT
<b>CAPACITY</b>	1000 lb
<b>WHEEL</b>	(2) 10" Moldon Rubber, (2) 6" Moldon Rubber

**WHEEL IMAGE**

BT Cast Iron Center Moldon Rubber Wheel

<b>WEIGHT</b>	82 lb
<b>OVERALL WIDTH</b>	24"
<b>OVERALL HEIGHT</b>	56"
<b>OVERALL DEPTH</b>	20.5"
<b>BOTTOM OF LOWERED CHIME HOOK</b>	28"
<b>DRUM TYPE</b>	Steel Drums

**MADE IN THE USA**