



1250 Welsh Rd

North Wales, PA 19454

Phone: 800.445.5681 • Fax: 800.346.5511

Email: info@wescomfg.com

PART NO. 240029, STEEL DRUM DOLLY



- All welded steel frame construction with reinforced outriggers.
- Four bolt on 3" swivel casters.
- I.D. varies among models.
- Models available for 30, 55, and 85 gallon drums.

Specifications

PART NUMBER	240029
MODEL	D3-HR
CAPACITY	900 lb
SWIVEL CASTER	(4) 3" Hard Rubber
CASTER RIG MATERIAL	Zinc Plate
I.D.	19"
DRUM SIZE	30 gal
DOLLY MATERIAL	Steel
OVERALL WIDTH	24"
OVERALL HEIGHT	6"
OVERALL DEPTH	24"
WEIGHT	18 lb



