



1250 Welsh Rd

North Wales, PA 19454

Phone: 800.445.5681 • Fax: 800.346.5511

Email: info@wescomfg.com

PART NO. 240031, STEEL DRUM DOLLY



- All welded steel frame construction with reinforced outriggers.
- Four bolt on 3" swivel casters.
- I.D. varies among models.
- Models available for 30, 55, and 85 gallon drums.

Specifications

PART NUMBER	240031
MODEL	D5-HR
CAPACITY	900 lb
SWIVEL CASTER	(4) 3" Hard Rubber
CASTER RIG MATERIAL	Zinc Plate
I.D.	24"
DRUM SIZE	55 gal
DOLLY MATERIAL	Steel
OVERALL WIDTH	28.5"
OVERALL HEIGHT	6"
OVERALL DEPTH	28.5"
WEIGHT	22 lb



