



1250 Welsh Rd

North Wales, PA 19454

Phone: 800.445.5681 • Fax: 800.346.5511

Email: info@wescomfg.com

PART NO. 240040, SPECIALTY DOLLY



- 3" hard rubber swivel casters
- Steel construction
- Removable tow handle
- Acts as sump for small leaks and spills
- Removable drain plug

Specifications

PART NUMBER	240040
MODEL	SSD
CAPACITY	900 lb
SWIVEL CASTER	(4) 3" Hard Rubber
CASTER RIG MATERIAL	Zinc Plate
SQUARE I.D.	23.625"
DOLLY MATERIAL	Steel
OVERALL WIDTH	25.75"
OVERALL HEIGHT	6"
OVERALL DEPTH	24.5"
WEIGHT	47 lb



MADE IN THE USA

