



1250 Welsh Rd

North Wales, PA 19454

Phone: 800.445.5681 • Fax: 800.346.5511

Email: info@wescomfg.com

PART NO. 260151, HYDRAULIC LITE-LIFT



- **1-year warranty.**
- Wesco® manufactured hydraulic Pedalift Jack, over 35 year of proven quality.
- Foot operated hydraulic pump.
- Release foot pedal for controlled lowering.
- Casters with wheel locks.
- Adjustable forks.

Specifications

PART NUMBER	260151
MODEL	LLHF
CAPACITY	500 lb
LIFT HEIGHT	54"
WIDTH FORKS	3"
LENGTH FORKS	19"
LOAD CENTER	10"
OVERALL WIDTH	20"
OVERALL HEIGHT	70.5"
OVERALL DEPTH	30"
WEIGHT	157 lb



CASTER (4) 5"

LOWERED HEIGHT 4.25"

FRONT LEG SPAN OUTSIDE DIAMETER 20"

THICKNESS FORKS 0.75"

FRONT LEG SPAN INSIDE DIAMETER 15.25"

MADE IN THE USA

