



Wesco Industrial Products, Inc.

1250 Welsh Rd

North Wales, PA 19454

Phone: 800.445.5681 • Fax: 800.346.5511

Email: info@wescomfg.com

PART NO. 261036, 3" X 40" FORK ADJUSTABLE SPAN STRADDLE POWERED STACKER



- 1-year warranty.
- Proven quality: Wesco® manufactured Hydraulic Cylinder.
- Battery and charger included.
- Forks lower to floor on all models.
- Extra deep (40") straddle legs and forks for lifting pallets.
- Versatile adjustable span straddle legs can be set from 34" to 50" inside dimension to handle most standard pallets.
- 110V AC models available. (Special order, NO cancellations or returns.)
- To order add AC to the end of the battery powered stacker part #.

Example:

Battery Powered #261036

110V AC Powered #261036AC

- Meets ANSI B56.10 specifications.
- Power Drive option available.

[Video](#) | [Specifications](#) | [5th Wheel Steering Option](#)

Video



Specifications



PART NUMBER	261036
MODEL	PASFL-76-40S
TYPE	Adjustable Straddle Fork Models
FRONT WHEEL	(2) 5" Phenolic
REAR SWIVEL CASTER	(2) 4" Phenolic
LIFT HEIGHT	76"
CAPACITY	1000 lb
WIDTH FORKS	3"
LENGTH FORKS	40"
ADJUSTABLE BASE LEG	34" to 50" I.D.
OVERALL WIDTH	54"
OVERALL HEIGHT	92"
OVERALL DEPTH	58.75"
WEIGHT	554 lb
MADE IN THE USA	

5th Wheel Steering Option

5TH WHEEL STEERING OPTION



5th Wheel Steering Option for easier mobility and precision steering in confined areas. Available only on 1,500 and 2,000 lb models. 8" locking polyurethane wheels. Spring loaded handle. Can be field installed. Order as separate option under Part # 261099

5th wheel steering option

