



1250 Welsh Rd

North Wales, PA 19454

Phone: 800.445.5681 • Fax: 800.346.5511

Email: [info@wescomfg.com](mailto:info@wescomfg.com)

## PART NO. 261044, 3" X 30" FORK / 36" O.D. FIXED BASE POWERED STACKER



- 1-year warranty.
- Proven quality: Wesco® manufactured Hydraulic Cylinder.
- Meets ANSI B56.10 specifications.
- Battery and charger included.
- Forks lower to floor on all models.
- Reinforced frame and fixed base.
- Double chain, lift support.
- Heavy-duty pump.
- Ergonomic "D" handles.
- 5th wheel and power drive options available.
- 110V AC models available (Special order no cancellations or returns).
- To order add AC to the end of the battery powered stacker part #.

Example:

Battery Powered #261044

110V AC Powered #261044AC

[Video](#) | [Specifications](#) | [5th Wheel Steering Option](#) | [Stacker Low Profile Outrigger Option](#)

### Video



## Specifications

<b>PART NUMBER</b>	261044
<b>MODEL</b>	PSFL-64-30-30S-2K
<b>LIFT HEIGHT</b>	64"
<b>CAPACITY</b>	2000 lb
<b>WIDTH FORKS</b>	3"
<b>LENGTH FORKS</b>	30"
<b>LOAD CENTER</b>	18"
<b>BASE LEG (ID/OD)</b>	30"/36"
<b>OVERALL HEIGHT</b>	83"
<b>WEIGHT</b>	571 lb
<b>ADJUSTABLE FORK MIN / MAX OD</b>	6" / 29"

**MADE IN THE USA**



## 5th Wheel Steering Option

### 5TH WHEEL STEERING OPTION




**5th Wheel Steering Option** for easier mobility & precision steering in confined areas. Available only on 1,500 and 2,000 lb models. 8" locking polyurethane wheels. Spring loader handle. Can be field installed. Order as separate option under Part # 261099

5th wheel steering option

## Stacker Low Profile Outrigger Option

## STACKER LOW PROFILE OUTRIGGER OPTION



Stacker Low Profile Outrigger Option