



Wesco Industrial Products, Inc.

1250 Welsh Rd

North Wales, PA 19454

Phone: 800.445.5681 • Fax: 800.346.5511

Email: [info@wescomfg.com](mailto:info@wescomfg.com)

## PART NO. 261051, 3" X 42" FORK / 56" O.D. FIXED BASE POWERED STACKER



- 1-year warranty.
- Proven quality: Wesco® manufactured Hydraulic Cylinder.
- Meets ANSI B56.10 specifications.
- Battery and charger included.
- Forks lower to floor on all models.
- Reinforced frame and fixed base.
- Double chain, lift support.
- Heavy-duty pump.
- Ergonomic "D" handles.
- 5th wheel and power drive options available.
- 110 V AC models available. (special order no cancellations or returns).
- To order add AC to the end of the battery powered stacker part #.

Example:

Battery Powered #261051

110V AC Powered #261051AC

[Video](#) | [Specifications](#) | [5th Wheel Steering Option](#)

### Video



## Specifications

|                                     |                   |
|-------------------------------------|-------------------|
| <b>PART NUMBER</b>                  | 261051            |
| <b>MODEL</b>                        | PSFL-76-42-50S-2K |
| <b>LIFT HEIGHT</b>                  | 76"               |
| <b>CAPACITY</b>                     | 2000 lb           |
| <b>WIDTH FORKS</b>                  | 3"                |
| <b>LENGTH FORKS</b>                 | 42"               |
| <b>LOAD CENTER</b>                  | 24"               |
| <b>BASE LEG (ID/OD)</b>             | 50"/56"           |
| <b>OVERALL HEIGHT</b>               | 94"               |
| <b>WEIGHT</b>                       | 647 lb            |
| <b>ADJUSTABLE FORK MIN / MAX OD</b> | 6"/29"            |

**MADE IN THE USA**



## 5th Wheel Steering Option

### 5TH WHEEL STEERING OPTION



5th Wheel Steering Option for easier mobility & precision steering in confined areas. Available only on 1,500 and 2,000 lb models. 8" locking polyurethane wheels. Spring loader handle. Can be field installed. Order as separate option under Part # 261099

5th wheel steering option